



# ALS Chemex

EXCELLENCE IN ANALYTICAL CHEMISTRY

Australian Laboratory Services Pty Ltd

32 Shand Street

Stafford

Brisbane QLD 4053

Phone: +61 (7) 3243 7222 Fax: +61 (7) 3243 7218 www.alschemex.com

## CERTIFICATE AD08102151

**Project:**

P.O. No.: 0404

This report is for 238 Drill Core samples submitted to our lab in Adelaide, SA, Australia on 28-JUL-2008.

The following have access to data associated with this certificate:

BARBARA ANDERSON  
B ANDERSON  
CHRIS DROWN

B ANDERSON  
BARBARA ANDERSON

BARBARA ANDERSON  
B ANDERSON

## SAMPLE PREPARATION

| ALS CODE | DESCRIPTION                    |
|----------|--------------------------------|
| WEI-21   | Received Sample Weight         |
| LOG-22   | Sample login - Rcd w/o BarCode |
| LEV-01   | Waste Disposal Levy            |
| PUL-QC   | Pulverizing QC Test            |
| PUL-23   | Pulv Sample - Split/Retain     |
| BAG-01   | Bulk Master for Storage        |
| SPL-21   | Split sample - riffle splitter |
| CRU-21   | Crush entire sample >70% -6 mm |

## ANALYTICAL PROCEDURES

| ALS CODE | DESCRIPTION                   | INSTRUMENT |
|----------|-------------------------------|------------|
| ME-ICP61 | 33 element four acid ICP-AES  | ICP-AES    |
| Au-AA25  | Ore Grade Au 30g FA AA finish | AAS        |

To: **ADELAIDE RESOURCES NL**  
**ATTN: BARBARA ANDERSON**  
**PO BOX 1210**  
**UNLEY BC SA 5061**

This is the Final Report and supersedes any preliminary report with this certificate number. Results apply to samples as submitted. All pages of this report have been checked and approved for release.

**Signature:**

Wayne Abbott, Operations Manager, Western Australia



# ALS Chemex

EXCELLENCE IN ANALYTICAL CHEMISTRY

Australian Laboratory Services Pty Ltd

32 Shand Street

Stafford

Brisbane QLD 4053

Phone: +61 (7) 3243 7222 Fax: +61 (7) 3243 7218 www.alschemex.com

## CERTIFICATE OF ANALYSIS AD08102151

| Method Analyte Units LOR | WEI-21 Recvd Wt. kg | PUL-QC Pass75um % | Au-AA25 Au ppm | ME-ICP61 Ag ppm | ME-ICP61 As ppm | ME-ICP61 Bi ppm | ME-ICP61 Co ppm | ME-ICP61 Cu ppm | ME-ICP61 Fe % | ME-ICP61 Pb ppm | ME-ICP61 S % | ME-ICP61 U ppm | ME-ICP61 Zn ppm |
|--------------------------|---------------------|-------------------|----------------|-----------------|-----------------|-----------------|-----------------|-----------------|---------------|-----------------|--------------|----------------|-----------------|
| Sample Description       | 0.02                | 0.01              | 0.01           | 0.5             | 5               | 2               | 1               | 1               | 0.01          | 2               | 0.01         | 10             | 2               |
| R3669                    | 2.53                |                   | <0.01          | <0.5            | <5              | <2              | 7               | 5               | 3.42          | 9               | 0.03         | <10            | 38              |
| R3670                    | 2.55                |                   | 0.01           | <0.5            | <5              | 2               | 12              | 4               | 3.78          | 11              | 0.11         | <10            | 68              |
| R3671                    | 2.62                |                   | 0.01           | <0.5            | 6               | 4               | 12              | 3               | 3.55          | 10              | 0.01         | <10            | 65              |
| R3672                    | 2.45                |                   | <0.01          | <0.5            | <5              | <2              | 13              | 4               | 3.30          | 4               | 0.06         | <10            | 81              |
| R3673                    | 2.55                | 95.0              | <0.01          | <0.5            | 9               | <2              | 12              | 2               | 2.88          | 6               | <0.01        | <10            | 71              |
| R3674                    | 2.46                |                   | <0.01          | <0.5            | 8               | 3               | 12              | 3               | 3.17          | 2               | 0.02         | <10            | 86              |
| R3675                    | 2.45                |                   | <0.01          | <0.5            | 8               | 3               | 9               | 6               | 3.21          | 9               | 0.23         | <10            | 84              |
| R3676                    | 2.66                |                   | <0.01          | <0.5            | 8               | 4               | 1               | 7               | 3.42          | 5               | 0.13         | <10            | 6               |
| R3677                    | 2.13                |                   | <0.01          | <0.5            | 10              | 2               | 5               | 6               | 4.02          | 5               | 0.08         | <10            | 26              |
| R3678                    | 2.56                |                   | <0.01          | <0.5            | <5              | 3               | 4               | 4               | 3.82          | 5               | 0.10         | <10            | 33              |
| R3679                    | 2.34                |                   | <0.01          | <0.5            | <5              | 2               | 8               | 3               | 3.91          | 4               | 0.05         | <10            | 63              |
| R3680                    | 0.08                |                   | 0.83           | 2.2             | 9               | 2               | 13              | 7030            | 5.04          | 15              | 0.83         | <10            | 74              |
| R3681                    | 2.46                |                   | <0.01          | <0.5            | <5              | <2              | 10              | 10              | 3.78          | 3               | 0.05         | <10            | 72              |
| R3682                    | 2.46                |                   | <0.01          | <0.5            | <5              | <2              | 9               | 6               | 3.31          | 3               | 0.03         | <10            | 69              |
| R3683                    | 2.48                |                   | <0.01          | <0.5            | <5              | 2               | 11              | 4               | 4.25          | 8               | 0.03         | <10            | 90              |
| R3684                    | 2.53                |                   | 0.01           | <0.5            | <5              | 2               | 9               | 2               | 3.46          | 4               | 0.03         | <10            | 68              |
| R3685                    | 2.52                |                   | 0.01           | <0.5            | <5              | 2               | 12              | 2               | 3.39          | 5               | 0.02         | <10            | 73              |
| R3686                    | 2.24                |                   | <0.01          | <0.5            | <5              | <2              | 10              | 2               | 3.41          | 5               | 0.04         | <10            | 73              |
| R3687                    | 1.97                |                   | <0.01          | <0.5            | <5              | <2              | 12              | 4               | 4.18          | 13              | 0.10         | <10            | 91              |
| R3688                    | 1.43                |                   | <0.01          | <0.5            | <5              | <2              | 9               | 2               | 4.08          | 5               | 0.02         | <10            | 73              |
| R3689                    | 2.44                |                   | 0.01           | <0.5            | <5              | <2              | 11              | 3               | 3.77          | 4               | 0.01         | <10            | 67              |
| R3690                    | 1.82                |                   | <0.01          | <0.5            | <5              | <2              | 11              | 2               | 3.35          | 5               | 0.01         | <10            | 66              |
| R3691                    | 1.76                |                   | <0.01          | <0.5            | 7               | 2               | 12              | 2               | 3.36          | 4               | 0.01         | <10            | 64              |
| R3692                    | 2.80                |                   | <0.01          | <0.5            | <5              | 2               | 12              | 1               | 4.15          | 4               | 0.01         | <10            | 85              |
| R3693                    | 3.32                |                   | <0.01          | <0.5            | <5              | 2               | 10              | 2               | 3.96          | 6               | 0.02         | <10            | 66              |
| R3694                    | 2.88                |                   | <0.01          | <0.5            | <5              | 2               | 10              | 1               | 3.59          | 5               | 0.01         | <10            | 63              |
| R3695                    | 2.79                |                   | <0.01          | <0.5            | <5              | <2              | 10              | 1               | 3.87          | 2               | 0.01         | <10            | 68              |
| R3696                    | 2.46                |                   | <0.01          | <0.5            | <5              | <2              | 11              | 2               | 3.90          | 4               | 0.04         | <10            | 75              |
| R3697                    | 2.21                |                   | <0.01          | <0.5            | <5              | <2              | 10              | 3               | 3.74          | 4               | 0.06         | <10            | 65              |
| R3698                    | 1.19                |                   | <0.01          | <0.5            | <5              | 2               | 8               | 2               | 3.13          | 5               | 0.01         | <10            | 53              |
| R3699                    | 2.56                |                   | <0.01          | <0.5            | 10              | <2              | 17              | 3               | 5.91          | 4               | 0.02         | <10            | 99              |
| R3700                    | 0.10                |                   | 0.65           | 1.4             | 11              | 4               | 12              | 4970            | 4.87          | 10              | 0.62         | <10            | 59              |
| R3701                    | 2.58                |                   | <0.01          | <0.5            | 8               | <2              | 41              | 8               | 11.45         | 6               | 0.03         | <10            | 208             |
| R3702                    | 2.74                |                   | <0.01          | <0.5            | 8               | 2               | 46              | 14              | 12.05         | 4               | 0.01         | <10            | 199             |
| R3703                    | 2.71                |                   | 0.01           | <0.5            | 11              | <2              | 38              | 4               | 12.00         | 9               | 0.04         | <10            | 135             |
| R3704                    | 2.78                |                   | <0.01          | <0.5            | 6               | <2              | 30              | 8               | 8.89          | 4               | 0.21         | 10             | 96              |
| R3705                    | 2.77                |                   | <0.01          | <0.5            | 7               | <2              | 26              | 5               | 11.30         | 3               | 0.09         | 10             | 68              |
| R3706                    | 2.76                |                   | <0.01          | <0.5            | <5              | <2              | 25              | 7               | 8.29          | 2               | 0.12         | 10             | 64              |
| R3707                    | 2.63                |                   | <0.01          | <0.5            | <5              | <2              | 25              | 7               | 8.44          | 3               | 0.07         | <10            | 64              |
| R3708                    | 2.76                |                   | 0.01           | <0.5            | 8               | 3               | 17              | 16              | 9.14          | 5               | 0.10         | <10            | 33              |



# ALS Chemex

EXCELLENCE IN ANALYTICAL CHEMISTRY

Australian Laboratory Services Pty Ltd

32 Shand Street

Stafford

Brisbane QLD 4053

Phone: +61 (7) 3243 7222 Fax: +61 (7) 3243 7218 www.alschemex.com

## CERTIFICATE OF ANALYSIS AD08102151

| Method Analyte Units LOR | WEI-21 Recvd Wt. kg | PUL-QC Pass75um % | Au-AA25 Au ppm | ME-ICP61 Ag ppm | ME-ICP61 As ppm | ME-ICP61 Bi ppm | ME-ICP61 Co ppm | ME-ICP61 Cu ppm | ME-ICP61 Fe % | ME-ICP61 Pb ppm | ME-ICP61 S % | ME-ICP61 U ppm | ME-ICP61 Zn ppm |
|--------------------------|---------------------|-------------------|----------------|-----------------|-----------------|-----------------|-----------------|-----------------|---------------|-----------------|--------------|----------------|-----------------|
| Sample Description       | 0.02                | 0.01              | 0.01           | 0.5             | 5               | 2               | 1               | 1               | 0.01          | 2               | 0.01         | 10             | 2               |
| R3709                    | 2.72                |                   | 0.06           | <0.5            | 7               | <2              | 25              | 11              | 17.10         | 2               | 0.06         | 10             | 52              |
| R3710                    | 2.32                |                   | 0.03           | <0.5            | 8               | 2               | 18              | 15              | 18.50         | 3               | 0.02         | 10             | 53              |
| R3711                    | 3.25                |                   | 0.01           | <0.5            | 6               | <2              | 29              | 8               | 12.05         | <2              | 0.02         | 10             | 211             |
| R3712                    | 2.77                |                   | 0.02           | <0.5            | 9               | <2              | 31              | 3               | 11.95         | 3               | 0.01         | 10             | 213             |
| R3713                    | 2.60                | 87.0              | <0.01          | <0.5            | <5              | <2              | 30              | 8               | 10.85         | <2              | 0.01         | 10             | 187             |
| R3714                    | 2.71                |                   | <0.01          | <0.5            | 7               | <2              | 39              | 4               | 13.65         | 3               | 0.04         | 10             | 236             |
| R3715                    | 2.66                |                   | 0.02           | <0.5            | <5              | <2              | 50              | 3               | 12.95         | <2              | 0.03         | 10             | 166             |
| R3716                    | 2.79                |                   | 0.02           | <0.5            | 6               | <2              | 38              | 7               | 11.05         | <2              | 0.01         | 10             | 113             |
| R3717                    | 2.78                |                   | <0.01          | <0.5            | <5              | <2              | 18              | 58              | 7.87          | <2              | 0.01         | 10             | 66              |
| R3718                    | 2.82                |                   | <0.01          | <0.5            | 8               | <2              | 32              | 27              | 9.75          | <2              | 0.10         | 10             | 83              |
| R3719                    | 2.85                |                   | 0.01           | <0.5            | <5              | <2              | 15              | 20              | 9.46          | <2              | 0.01         | 10             | 42              |
| R3720                    | 0.09                |                   | 0.30           | 1.1             | <5              | 2               | 6               | 3170            | 3.29          | 23              | 0.37         | 10             | 62              |
| R3721                    | 2.76                |                   | 0.09           | <0.5            | 7               | <2              | 65              | 8               | 18.65         | 6               | 0.02         | <10            | 188             |
| R3722                    | 2.79                |                   | 0.02           | <0.5            | <5              | <2              | 21              | 5               | 8.96          | <2              | 0.02         | <10            | 57              |
| R3723                    | 2.79                |                   | <0.01          | <0.5            | <5              | <2              | 28              | 2               | 10.30         | <2              | 0.01         | <10            | 65              |
| R3724                    | 2.88                |                   | <0.01          | <0.5            | 5               | <2              | 30              | 3               | 13.95         | 5               | 0.02         | <10            | 80              |
| R3725                    | 2.91                |                   | 0.04           | <0.5            | 7               | <2              | 25              | 25              | 22.5          | 9               | 0.04         | 10             | 86              |
| R3726                    | 3.03                |                   | 0.04           | <0.5            | 9               | <2              | 10              | 38              | 21.6          | 3               | 0.06         | 10             | 62              |
| R3727                    | 3.20                |                   | <0.01          | <0.5            | <5              | <2              | 3               | 39              | 22.3          | <2              | 0.02         | 10             | 15              |
| R3728                    | 3.29                |                   | 0.01           | <0.5            | 21              | 3               | 29              | 1340            | 23.1          | 13              | 0.75         | 10             | 8               |
| R3729                    | 3.19                |                   | 0.05           | 0.9             | 65              | 10              | 92              | 345             | 19.20         | 46              | 2.19         | 10             | 9               |
| R3730                    | 3.07                |                   | 0.02           | <0.5            | 33              | 3               | 35              | 1750            | 17.20         | 17              | 1.03         | <10            | 13              |
| R3731                    | 2.94                |                   | 0.02           | <0.5            | 19              | 2               | 21              | 481             | 14.65         | 12              | 0.70         | <10            | 8               |
| R3732                    | 3.06                |                   | 0.05           | 0.7             | 199             | 13              | 97              | 197             | 15.35         | 24              | 3.06         | 10             | 10              |
| R3733                    | 2.92                |                   | 0.01           | <0.5            | 15              | 5               | 22              | 384             | 14.35         | 13              | 0.53         | 10             | 10              |
| R3734                    | 3.17                |                   | 0.01           | <0.5            | 20              | 3               | 37              | 2090            | 21.8          | 9               | 0.90         | 10             | 14              |
| R3735                    | 3.13                |                   | 0.07           | 0.6             | 66              | 22              | 128             | 6280            | 23.1          | 33              | 4.33         | 10             | 9               |
| R3736                    | 3.03                |                   | 0.01           | <0.5            | 23              | <2              | 14              | 621             | 21.4          | 16              | 0.43         | <10            | 10              |
| R3737                    | 3.24                |                   | 0.01           | <0.5            | 19              | 4               | 22              | 998             | 25.0          | 14              | 0.45         | 10             | 8               |
| R3738                    | 2.92                |                   | 0.02           | 0.5             | 31              | 5               | 49              | 303             | 17.00         | 23              | 0.88         | 10             | 7               |
| R3739                    | 3.11                |                   | 0.17           | <0.5            | 17              | <2              | 10              | 2080            | 23.8          | 26              | 0.41         | <10            | 21              |
| R3740                    | 0.09                |                   | 0.63           | 1.5             | 10              | <2              | 13              | 5520            | 5.59          | 20              | 0.68         | <10            | 85              |
| R3741                    | 3.10                |                   | 0.03           | 0.5             | 41              | <2              | 5               | 433             | 25.1          | 149             | 0.21         | <10            | 154             |
| R3742                    | 2.92                |                   | <0.01          | <0.5            | 17              | <2              | 5               | 570             | 20.1          | 39              | 0.23         | <10            | 26              |
| R3743                    | 2.83                |                   | 0.02           | 0.6             | 95              | 14              | 79              | 733             | 15.65         | 63              | 2.52         | <10            | 26              |
| R3744                    | 2.71                |                   | <0.01          | <0.5            | 17              | <2              | 12              | 54              | 10.95         | 22              | 0.32         | <10            | 19              |
| R3745                    | 2.74                |                   | <0.01          | <0.5            | 16              | <2              | 8               | 53              | 9.12          | 16              | 0.39         | <10            | 19              |
| R3746                    | 2.63                |                   | <0.01          | <0.5            | 8               | <2              | 5               | 315             | 10.55         | 22              | 1.22         | <10            | 17              |
| R3747                    | 2.38                |                   | <0.01          | <0.5            | <5              | <2              | <1              | 12              | 6.86          | 6               | 0.05         | <10            | 9               |
| R3748                    | 2.32                |                   | 0.01           | <0.5            | 56              | 2               | 15              | 19              | 8.11          | 15              | 0.92         | <10            | 8               |



# ALS Chemex

EXCELLENCE IN ANALYTICAL CHEMISTRY

Australian Laboratory Services Pty Ltd

32 Shand Street

Stafford

Brisbane QLD 4053

Phone: +61 (7) 3243 7222 Fax: +61 (7) 3243 7218 www.alschemex.com

## CERTIFICATE OF ANALYSIS AD08102151

| Method Analyte Units LOR | WEI-21 Recvd Wt. kg | PUL-QC Pass75um % | Au-AA25 Au ppm | ME-ICP61 Ag ppm | ME-ICP61 As ppm | ME-ICP61 Bi ppm | ME-ICP61 Co ppm | ME-ICP61 Cu ppm | ME-ICP61 Fe % | ME-ICP61 Pb ppm | ME-ICP61 S % | ME-ICP61 U ppm | ME-ICP61 Zn ppm |
|--------------------------|---------------------|-------------------|----------------|-----------------|-----------------|-----------------|-----------------|-----------------|---------------|-----------------|--------------|----------------|-----------------|
| Sample Description       | 0.02                | 0.01              | 0.01           | 0.5             | 5               | 2               | 1               | 1               | 0.01          | 2               | 0.01         | 10             | 2               |
| R3749                    | 1.48                |                   | <0.01          | <0.5            | <5              | <2              | 1               | 37              | 5.32          | 8               | 0.08         | <10            | 7               |
| R3750                    | 2.42                |                   | 0.01           | 0.6             | 44              | <2              | 16              | 37              | 7.25          | 31              | 1.50         | <10            | 9               |
| R3751                    | 2.95                |                   | 0.01           | <0.5            | 22              | <2              | 8               | 25              | 11.20         | 26              | 0.69         | <10            | 11              |
| R3752                    | 2.67                |                   | 0.03           | <0.5            | <5              | <2              | <1              | 4               | 6.36          | 5               | 0.05         | <10            | 8               |
| R3753                    | 2.59                | 92.0              | <0.01          | <0.5            | 9               | <2              | <1              | 4               | 8.43          | 9               | 0.12         | <10            | 8               |
| R3754                    | 2.72                |                   | <0.01          | <0.5            | <5              | <2              | <1              | 5               | 6.76          | 7               | 0.06         | <10            | 12              |
| R3755                    | 2.75                |                   | 0.01           | <0.5            | 18              | <2              | 10              | 15              | 5.59          | 30              | 0.92         | <10            | 9               |
| R3756                    | 2.80                |                   | <0.01          | <0.5            | 11              | <2              | 9               | 8               | 5.35          | 16              | 0.42         | <10            | 8               |
| R3757                    | 2.75                |                   | <0.01          | <0.5            | 15              | <2              | 7               | 18              | 6.18          | 20              | 0.49         | <10            | 10              |
| R3758                    | 2.85                |                   | 0.01           | <0.5            | 8               | <2              | 2               | 9               | 6.67          | 12              | 0.35         | <10            | 9               |
| R3759                    | 2.93                |                   | 0.01           | 0.6             | 67              | 4               | 27              | 66              | 9.55          | 48              | 3.32         | <10            | 10              |
| R3760                    | 0.12                |                   | 0.84           | 2.1             | 11              | <2              | 13              | 7040            | 5.15          | 16              | 0.87         | <10            | 70              |
| R3761                    | 2.88                |                   | 0.01           | 0.6             | 71              | <2              | 17              | 23              | 8.56          | 40              | 2.08         | <10            | 11              |
| R3762                    | 2.72                |                   | 0.01           | <0.5            | 10              | <2              | 4               | 104             | 4.55          | 17              | 0.22         | <10            | 10              |
| R3763                    | 2.74                |                   | 0.01           | <0.5            | 26              | <2              | 6               | 462             | 10.10         | 46              | 0.73         | <10            | 14              |
| R3764                    | 3.12                |                   | 0.01           | 2.3             | 347             | 12              | 98              | 586             | 23.1          | 272             | >10.0        | 20             | 61              |
| R3765                    | 2.42                |                   | 0.01           | 0.6             | 152             | <2              | 23              | 138             | 12.85         | 61              | 3.38         | <10            | 134             |
| R3766                    | 2.54                |                   | <0.01          | 0.5             | 138             | 2               | 18              | 61              | 11.40         | 39              | 1.88         | <10            | 150             |
| R3767                    | 2.74                |                   | 0.01           | 0.8             | 129             | 3               | 21              | 815             | 18.65         | 30              | 1.95         | <10            | 252             |
| R3768                    | 2.61                |                   | 0.02           | 2.0             | 218             | 16              | 59              | 4110            | 18.05         | 147             | 3.23         | <10            | 276             |
| R3769                    | 2.88                |                   | 0.06           | 1.5             | 483             | 29              | 53              | 2650            | 21.1          | 156             | >10.0        | <10            | 218             |
| R3770                    | 2.86                |                   | 0.09           | 1.1             | 312             | 25              | 38              | 1900            | 22.0          | 103             | >10.0        | <10            | 218             |
| R3771                    | 2.52                |                   | 0.02           | 0.6             | 123             | 10              | 23              | 1150            | 16.40         | 27              | 2.28         | <10            | 208             |
| R3772                    | 2.45                |                   | 0.03           | 0.8             | 130             | 13              | 61              | 347             | 19.40         | 57              | 3.32         | 10             | 251             |
| R3773                    | 1.86                |                   | 0.07           | 0.7             | 256             | 17              | 62              | 82              | 18.35         | 47              | 2.94         | <10            | 259             |
| R3774                    | 2.66                |                   | 0.02           | <0.5            | 99              | 10              | 40              | 450             | 10.75         | 17              | 0.97         | 10             | 167             |
| R3775                    | 2.56                |                   | 0.02           | <0.5            | 449             | 10              | 133             | 291             | 20.8          | 23              | 1.85         | 10             | 191             |
| R3776                    | 1.29                |                   | 0.07           | 0.5             | 110             | 25              | 55              | 377             | 20.9          | 27              | 1.24         | 10             | 148             |
| R3777                    | 3.16                |                   | 0.03           | <0.5            | 35              | 21              | 24              | 459             | 18.70         | 16              | 0.50         | 10             | 133             |
| R3778                    | 3.25                |                   | 0.03           | <0.5            | 33              | 25              | 29              | 577             | 19.35         | 8               | 0.41         | 10             | 145             |
| R3779                    | 2.62                |                   | 0.01           | <0.5            | 12              | <2              | 28              | 76              | 12.85         | 2               | 0.08         | 10             | 164             |
| R3780                    | 0.09                |                   | 0.31           | 1.1             | <5              | 2               | 5               | 3220            | 3.31          | 23              | 0.38         | 10             | 63              |
| R3781                    | 2.73                |                   | 0.01           | <0.5            | 36              | 5               | 25              | 463             | 12.25         | 12              | 0.65         | 10             | 154             |
| R3782                    | 2.75                |                   | 0.05           | <0.5            | 52              | 15              | 29              | 319             | 14.40         | 15              | 1.27         | 10             | 162             |
| R3783                    | 2.68                |                   | 0.06           | 0.6             | 57              | 23              | 25              | 879             | 11.10         | 25              | 1.68         | 10             | 130             |
| R3784                    | 2.73                |                   | 0.02           | <0.5            | 88              | 4               | 27              | 648             | 10.45         | 17              | 0.59         | 10             | 140             |
| R3785                    | 2.72                |                   | 0.01           | <0.5            | 46              | 3               | 27              | 826             | 11.70         | 19              | 0.45         | 20             | 167             |
| R3786                    | 2.66                |                   | 0.01           | <0.5            | 58              | 4               | 40              | 98              | 12.35         | 19              | 0.63         | 20             | 187             |
| R3787                    | 2.77                |                   | <0.01          | <0.5            | 15              | 2               | 28              | 204             | 11.00         | 11              | 0.22         | 10             | 151             |
| R3788                    | 2.71                |                   | 0.01           | <0.5            | 18              | 3               | 29              | 361             | 13.55         | 14              | 0.18         | 10             | 154             |



# ALS Chemex

EXCELLENCE IN ANALYTICAL CHEMISTRY

Australian Laboratory Services Pty Ltd

32 Shand Street

Stafford

Brisbane QLD 4053

Phone: +61 (7) 3243 7222 Fax: +61 (7) 3243 7218 www.alschemex.com

## CERTIFICATE OF ANALYSIS AD08102151

| Method<br>Analyte<br>Units<br>LOR | WEI-21<br>Recvd Wt.<br>kg | PUL-QC<br>Pass75um<br>% | Au-AA25<br>Au<br>ppm | ME-ICP61<br>Ag<br>ppm | ME-ICP61<br>As<br>ppm | ME-ICP61<br>Bi<br>ppm | ME-ICP61<br>Co<br>ppm | ME-ICP61<br>Cu<br>ppm | ME-ICP61<br>Fe<br>% | ME-ICP61<br>Pb<br>ppm | ME-ICP61<br>S<br>% | ME-ICP61<br>U<br>ppm | ME-ICP61<br>Zn<br>ppm |
|-----------------------------------|---------------------------|-------------------------|----------------------|-----------------------|-----------------------|-----------------------|-----------------------|-----------------------|---------------------|-----------------------|--------------------|----------------------|-----------------------|
| Sample Description                | 0.02                      | 0.01                    | 0.01                 | 0.5                   | 5                     | 2                     | 1                     | 1                     | 0.01                | 2                     | 0.01               | 10                   | 2                     |
| R3789                             | 2.73                      |                         | 0.01                 | <0.5                  | 10                    | <2                    | 34                    | 64                    | 13.55               | 8                     | 0.07               | 10                   | 170                   |
| R3790                             | 2.98                      |                         | 0.02                 | 1.1                   | 79                    | 24                    | 130                   | 81                    | 20.9                | 15                    | 0.59               | 10                   | 156                   |
| R3791                             | 2.89                      |                         | 0.02                 | <0.5                  | 18                    | 10                    | 71                    | 243                   | 19.45               | 11                    | 0.34               | 10                   | 173                   |
| R3792                             | 2.77                      |                         | 0.01                 | <0.5                  | 29                    | 11                    | 49                    | 79                    | 15.30               | 5                     | 0.15               | 10                   | 109                   |
| R3793                             | 2.69                      | 86.0                    | 0.01                 | <0.5                  | 24                    | 2                     | 94                    | 35                    | 12.40               | 3                     | 0.13               | 10                   | 147                   |
| R3794                             | 2.81                      |                         | 0.01                 | <0.5                  | 26                    | 13                    | 177                   | 80                    | 14.90               | 6                     | 0.18               | 10                   | 124                   |
| R3795                             | 2.64                      |                         | 0.01                 | <0.5                  | 43                    | 6                     | 141                   | 157                   | 13.40               | 2                     | 0.24               | 10                   | 192                   |
| R3796                             | 2.69                      |                         | 0.02                 | 0.5                   | 6                     | 5                     | 63                    | 78                    | 11.80               | 6                     | 0.05               | 10                   | 182                   |
| R3797                             | 2.60                      |                         | 0.01                 | <0.5                  | <5                    | 6                     | 76                    | 21                    | 9.35                | 7                     | 0.02               | 10                   | 155                   |
| R3798                             | 2.58                      |                         | 0.05                 | <0.5                  | 6                     | <2                    | 72                    | 75                    | 10.70               | 2                     | 0.05               | 10                   | 185                   |
| R3799                             | 2.71                      |                         | 0.12                 | 0.6                   | <5                    | 2                     | 87                    | 13                    | 11.90               | 8                     | 0.02               | 10                   | 227                   |
| R3800                             | 0.09                      |                         | 0.64                 | 1.7                   | 9                     | 3                     | 11                    | 5180                  | 4.84                | 9                     | 0.64               | 10                   | 60                    |
| R3801                             | 2.67                      |                         | 0.01                 | <0.5                  | 10                    | 2                     | 76                    | 68                    | 10.30               | 3                     | 0.08               | 10                   | 178                   |
| R3802                             | 2.08                      |                         | 0.02                 | <0.5                  | <5                    | <2                    | 3                     | 6                     | 2.55                | <2                    | 0.02               | <10                  | 9                     |
| R3803                             | 2.55                      |                         | 0.01                 | <0.5                  | 6                     | <2                    | 71                    | 6                     | 9.01                | 6                     | 0.02               | 10                   | 191                   |
| R3804                             | 2.71                      |                         | 0.02                 | <0.5                  | <5                    | <2                    | 62                    | 40                    | 10.35               | 4                     | 0.03               | 10                   | 210                   |
| R3805                             | 3.25                      |                         | 0.04                 | <0.5                  | 88                    | 19                    | 55                    | 776                   | 22.6                | 9                     | 0.46               | 10                   | 127                   |
| R3806                             | 2.41                      |                         | 0.03                 | 0.9                   | 42                    | 47                    | 79                    | 275                   | 10.85               | 11                    | 0.50               | 10                   | 220                   |
| R3807                             | 2.29                      |                         | 0.02                 | 0.8                   | 5                     | 57                    | 60                    | 38                    | 12.55               | 12                    | 0.03               | 10                   | 278                   |
| R3808                             | 2.67                      |                         | 0.06                 | <0.5                  | 7                     | 5                     | 50                    | 17                    | 10.60               | 2                     | 0.04               | 10                   | 240                   |
| R3809                             | 2.59                      |                         | 0.01                 | 0.5                   | 7                     | 6                     | 49                    | 21                    | 12.55               | 8                     | 0.02               | <10                  | 253                   |
| R3810                             | 2.44                      |                         | 0.03                 | <0.5                  | 17                    | 9                     | 28                    | 42                    | 7.68                | 37                    | 0.30               | <10                  | 140                   |
| R3811                             | 2.66                      |                         | 0.04                 | <0.5                  | 11                    | 4                     | 23                    | 8                     | 7.45                | 5                     | 0.09               | <10                  | 123                   |
| R3812                             | 2.52                      |                         | 0.01                 | <0.5                  | <5                    | 2                     | 14                    | 3                     | 5.52                | 4                     | 0.02               | <10                  | 83                    |
| R3813                             | 2.53                      |                         | <0.01                | <0.5                  | 18                    | 7                     | 15                    | 12                    | 5.73                | 4                     | 0.13               | <10                  | 81                    |
| R3814                             | 2.61                      |                         | <0.01                | <0.5                  | 7                     | <2                    | 14                    | 1                     | 5.49                | 3                     | 0.01               | <10                  | 76                    |
| R3815                             | 2.55                      |                         | <0.01                | <0.5                  | 6                     | <2                    | 12                    | 5                     | 5.10                | 5                     | 0.02               | <10                  | 63                    |
| R3816                             | 2.57                      |                         | 0.04                 | <0.5                  | 9                     | 3                     | 15                    | 2                     | 5.43                | 4                     | 0.02               | <10                  | 72                    |
| R3817                             | 2.52                      |                         | <0.01                | <0.5                  | 5                     | <2                    | 10                    | 1                     | 4.21                | 6                     | <0.01              | <10                  | 53                    |
| R3818                             | 2.54                      |                         | <0.01                | <0.5                  | 10                    | <2                    | 19                    | <1                    | 6.18                | 6                     | 0.01               | <10                  | 91                    |
| R3819                             | 2.60                      |                         | <0.01                | <0.5                  | 9                     | 5                     | 30                    | 2                     | 8.99                | 10                    | 0.03               | <10                  | 138                   |
| R3820                             | 0.10                      |                         | 0.76                 | 2.2                   | 9                     | 2                     | 13                    | 7100                  | 5.32                | 18                    | 0.86               | <10                  | 74                    |
| R3821                             | 2.58                      |                         | <0.01                | <0.5                  | <5                    | 3                     | 18                    | 8                     | 5.98                | 4                     | 0.02               | <10                  | 86                    |
| R3822                             | 2.55                      |                         | 0.01                 | <0.5                  | <5                    | <2                    | 14                    | 3                     | 4.88                | 3                     | 0.01               | <10                  | 67                    |
| R3823                             | 2.41                      |                         | 0.02                 | <0.5                  | <5                    | 3                     | 15                    | 1                     | 5.12                | 5                     | <0.01              | <10                  | 72                    |
| R3824                             | 2.53                      |                         | <0.01                | <0.5                  | <5                    | 3                     | 31                    | <1                    | 7.67                | 7                     | <0.01              | <10                  | 133                   |
| R3825                             | 2.53                      |                         | <0.01                | <0.5                  | 10                    | 6                     | 12                    | 2                     | 4.37                | 4                     | 0.03               | <10                  | 55                    |
| R3826                             | 2.60                      |                         | <0.01                | <0.5                  | <5                    | <2                    | 13                    | <1                    | 5.02                | 5                     | 0.01               | <10                  | 63                    |
| R3827                             | 2.57                      |                         | <0.01                | <0.5                  | <5                    | 3                     | 14                    | <1                    | 5.36                | 8                     | 0.01               | <10                  | 67                    |
| R3828                             | 2.50                      |                         | <0.01                | <0.5                  | 5                     | 4                     | 11                    | <1                    | 4.57                | 6                     | 0.01               | <10                  | 52                    |



# ALS Chemex

EXCELLENCE IN ANALYTICAL CHEMISTRY

Australian Laboratory Services Pty Ltd

32 Shand Street

Stafford

Brisbane QLD 4053

Phone: +61 (7) 3243 7222 Fax: +61 (7) 3243 7218 www.alschemex.com

## CERTIFICATE OF ANALYSIS AD08102151

| Method Analyte Units LOR | WEI-21 Recvd Wt. kg | PUL-QC Pass75um % | Au-AA25 Au ppm | ME-ICP61 Ag ppm | ME-ICP61 As ppm | ME-ICP61 Bi ppm | ME-ICP61 Co ppm | ME-ICP61 Cu ppm | ME-ICP61 Fe % | ME-ICP61 Pb ppm | ME-ICP61 S % | ME-ICP61 U ppm | ME-ICP61 Zn ppm |
|--------------------------|---------------------|-------------------|----------------|-----------------|-----------------|-----------------|-----------------|-----------------|---------------|-----------------|--------------|----------------|-----------------|
| Sample Description       | 0.02                | 0.01              | 0.01           | 0.5             | 5               | 2               | 1               | 1               | 0.01          | 2               | 0.01         | 10             | 2               |
| R3829                    | 2.49                |                   | <0.01          | <0.5            | 11              | 4               | 13              | 1               | 4.63          | 6               | 0.01         | <10            | 53              |
| R3830                    | 2.38                |                   | 0.01           | <0.5            | 6               | 3               | 12              | 1               | 4.47          | 4               | <0.01        | <10            | 55              |
| R3831                    | 2.40                |                   | <0.01          | <0.5            | <5              | 4               | 13              | 3               | 4.84          | 10              | 0.02         | <10            | 63              |
| R3832                    | 2.53                |                   | 0.02           | <0.5            | <5              | <2              | 11              | 1               | 4.37          | 3               | 0.01         | <10            | 55              |
| R3833                    | 2.63                | 90.0              | 0.01           | <0.5            | <5              | 2               | 13              | <1              | 4.45          | 4               | <0.01        | <10            | 61              |
| R3834                    | 2.42                |                   | <0.01          | <0.5            | <5              | <2              | 14              | <1              | 4.68          | 3               | <0.01        | <10            | 70              |
| R3835                    | 2.54                |                   | <0.01          | <0.5            | 5               | 11              | 21              | 197             | 6.06          | 2               | 0.02         | <10            | 102             |
| R3836                    | 2.49                |                   | 0.01           | <0.5            | 5               | 7               | 27              | 781             | 8.11          | 5               | 0.09         | <10            | 122             |
| R3837                    | 2.42                |                   | <0.01          | <0.5            | <5              | 10              | 23              | 1540            | 7.02          | 4               | 0.17         | <10            | 88              |
| R3838                    | 1.79                |                   | 0.17           | 1.4             | <5              | 52              | 33              | 3840            | 9.69          | 8               | 0.40         | <10            | 107             |
| R3839                    | 3.33                |                   | 0.07           | <0.5            | <5              | 11              | 24              | 5530            | 7.91          | 5               | 0.61         | <10            | 73              |
| R3840                    | 0.11                |                   | 0.38           | 1.0             | 5               | 2               | 6               | 3230            | 3.59          | 26              | 0.40         | <10            | 61              |
| R3841                    | 2.55                |                   | 0.07           | <0.5            | <5              | 7               | 30              | 1780            | 9.00          | 5               | 0.18         | <10            | 82              |
| R3842                    | 2.63                |                   | <0.01          | <0.5            | 6               | 7               | 25              | 1500            | 7.72          | 6               | 0.15         | <10            | 70              |
| R3843                    | 2.50                |                   | 0.01           | <0.5            | <5              | 6               | 24              | 1610            | 8.51          | 3               | 0.17         | <10            | 62              |
| R3844                    | 2.54                |                   | 0.12           | <0.5            | 8               | 18              | 24              | 1260            | 7.92          | 5               | 0.13         | <10            | 63              |
| R3845                    | 2.59                |                   | 2.64           | 4.6             | <5              | 272             | 26              | 7050            | 8.68          | 16              | 0.73         | <10            | 67              |
| R3846                    | 2.51                |                   | 4.10           | 5.7             | 5               | 231             | 31              | 5990            | 9.76          | 21              | 0.69         | <10            | 74              |
| R3847                    | 2.50                |                   | 3.75           | <0.5            | <5              | 19              | 20              | 4910            | 6.55          | 4               | 0.52         | <10            | 45              |
| R3848                    | 2.52                |                   | 0.47           | <0.5            | <5              | 22              | 21              | 3150            | 6.83          | 4               | 0.33         | <10            | 47              |
| R3849                    | 2.50                |                   | 0.07           | 1.0             | <5              | 48              | 19              | 700             | 6.68          | 13              | 0.08         | <10            | 46              |
| R3850                    | 2.53                |                   | 0.07           | <0.5            | <5              | <2              | 18              | 305             | 6.14          | 4               | 0.03         | <10            | 48              |
| R3851                    | 2.49                |                   | 0.01           | <0.5            | 8               | <2              | 19              | 1580            | 6.20          | 4               | 0.19         | <10            | 52              |
| R3852                    | 2.49                |                   | <0.01          | <0.5            | <5              | <2              | 18              | 44              | 6.40          | 16              | 0.01         | <10            | 66              |
| R3853                    | 2.53                |                   | <0.01          | <0.5            | 6               | <2              | 18              | 85              | 6.05          | 4               | 0.01         | <10            | 50              |
| R3854                    | 2.53                |                   | 0.04           | <0.5            | <5              | <2              | 14              | 62              | 5.04          | 8               | 0.02         | <10            | 47              |
| R3855                    | 2.55                |                   | 0.04           | <0.5            | <5              | <2              | 19              | 159             | 6.92          | 7               | 0.02         | <10            | 55              |
| R3856                    | 2.53                |                   | 0.02           | <0.5            | 6               | 2               | 18              | 653             | 7.07          | 5               | 0.08         | <10            | 52              |
| R3857                    | 2.53                |                   | <0.01          | <0.5            | <5              | 2               | 21              | 21              | 7.70          | 5               | 0.01         | <10            | 64              |
| R3858                    | 2.48                |                   | <0.01          | <0.5            | 6               | <2              | 16              | 6               | 5.32          | 2               | 0.01         | <10            | 46              |
| R3859                    | 2.55                |                   | <0.01          | <0.5            | 5               | 2               | 21              | 1340            | 7.15          | 3               | 0.22         | <10            | 61              |
| R3860                    | 0.10                |                   | 0.29           | 1.0             | 9               | <2              | 6               | 3260            | 3.43          | 25              | 0.37         | <10            | 63              |
| R3861                    | 2.54                |                   | <0.01          | <0.5            | <5              | <2              | 20              | 357             | 6.94          | 4               | 0.04         | <10            | 55              |
| R3862                    | 2.56                |                   | 0.05           | <0.5            | <5              | 2               | 31              | 328             | 8.59          | 5               | 0.04         | <10            | 71              |
| R3863                    | 2.51                |                   | 0.08           | <0.5            | 8               | <2              | 23              | 928             | 7.89          | 4               | 0.10         | <10            | 50              |
| R3864                    | 2.57                |                   | 0.07           | <0.5            | <5              | 3               | 26              | 784             | 8.32          | 5               | 0.09         | <10            | 57              |
| R3865                    | 2.52                |                   | 0.06           | <0.5            | 6               | 2               | 32              | 1710            | 9.65          | 4               | 0.21         | <10            | 68              |
| R3866                    | 2.51                |                   | 0.19           | <0.5            | <5              | 2               | 27              | 2250            | 8.51          | <2              | 0.24         | <10            | 68              |
| R3867                    | 2.47                |                   | 0.06           | <0.5            | 7               | 3               | 19              | 484             | 6.31          | 4               | 0.07         | <10            | 49              |
| R3868                    | 2.31                |                   | 0.11           | <0.5            | 8               | 22              | 15              | 178             | 5.57          | 7               | 0.05         | <10            | 39              |



# ALS Chemex

EXCELLENCE IN ANALYTICAL CHEMISTRY

Australian Laboratory Services Pty Ltd

32 Shand Street

Stafford

Brisbane QLD 4053

Phone: +61 (7) 3243 7222 Fax: +61 (7) 3243 7218 www.alschemex.com

## CERTIFICATE OF ANALYSIS AD08102151

| Method Analyte Units LOR | WEI-21 Recvd Wt. kg | PUL-QC Pass75um % | Au-AA25 Au ppm | ME-ICP61 Ag ppm | ME-ICP61 As ppm | ME-ICP61 Bi ppm | ME-ICP61 Co ppm | ME-ICP61 Cu ppm | ME-ICP61 Fe % | ME-ICP61 Pb ppm | ME-ICP61 S % | ME-ICP61 U ppm | ME-ICP61 Zn ppm |
|--------------------------|---------------------|-------------------|----------------|-----------------|-----------------|-----------------|-----------------|-----------------|---------------|-----------------|--------------|----------------|-----------------|
| Sample Description       | 0.02                | 0.01              | 0.01           | 0.5             | 5               | 2               | 1               | 1               | 0.01          | 2               | 0.01         | 10             | 2               |
| R3869                    | 2.50                |                   | 0.04           | <0.5            | 11              | 2               | 22              | 2100            | 7.37          | 2               | 0.27         | <10            | 63              |
| R3870                    | 2.57                |                   | 0.02           | <0.5            | <5              | 3               | 23              | 1180            | 7.24          | 2               | 0.13         | <10            | 64              |
| R3871                    | 2.56                |                   | 0.66           | <0.5            | 6               | 2               | 20              | 133             | 7.40          | 5               | 0.02         | <10            | 60              |
| R3872                    | 2.48                |                   | 0.24           | 0.6             | 7               | 17              | 15              | 539             | 5.92          | 11              | 0.06         | <10            | 50              |
| R3873                    | 2.48                | 95.0              | 0.05           | <0.5            | <5              | 4               | 19              | 47              | 7.15          | 7               | 0.01         | <10            | 62              |
| R3874                    | 2.57                |                   | <0.01          | <0.5            | <5              | <2              | 26              | 6               | 7.57          | 3               | 0.01         | <10            | 76              |
| R3875                    | 2.51                |                   | <0.01          | <0.5            | <5              | 3               | 27              | 1020            | 8.30          | 4               | 0.11         | <10            | 65              |
| R3876                    | 2.55                |                   | 0.02           | <0.5            | <5              | <2              | 22              | 1770            | 7.62          | 4               | 0.19         | <10            | 54              |
| R3877                    | 2.60                |                   | <0.01          | <0.5            | <5              | 3               | 15              | 33              | 5.83          | 4               | 0.01         | <10            | 49              |
| R3878                    | 2.49                |                   | 0.03           | <0.5            | <5              | <2              | 18              | 47              | 6.34          | 4               | 0.01         | <10            | 57              |
| R3879                    | 2.57                |                   | <0.01          | <0.5            | 6               | <2              | 17              | 84              | 5.80          | 2               | 0.01         | 10             | 61              |
| R3880                    | 0.09                |                   | 0.60           | 1.4             | 6               | 4               | 11              | 5080            | 4.66          | 7               | 0.61         | 10             | 62              |
| R3881                    | 2.53                |                   | 0.31           | <0.5            | <5              | 4               | 16              | 4670            | 5.59          | <2              | 0.50         | 10             | 56              |
| R3882                    | 2.48                |                   | 0.41           | <0.5            | <5              | <2              | 12              | 37              | 4.55          | 2               | 0.02         | 10             | 44              |
| R3883                    | 2.07                |                   | <0.01          | <0.5            | <5              | <2              | 15              | 5               | 5.41          | <2              | 0.01         | 10             | 55              |
| R3884                    | 2.90                |                   | 0.16           | <0.5            | <5              | <2              | 18              | 150             | 5.67          | <2              | 0.02         | 10             | 63              |
| R3885                    | 2.44                |                   | 1.04           | <0.5            | <5              | 12              | 18              | 2320            | 5.45          | 4               | 0.25         | 10             | 57              |
| R3886                    | 2.46                |                   | 0.68           | <0.5            | <5              | 5               | 18              | 3340            | 5.64          | 2               | 0.36         | 10             | 54              |
| R3887                    | 2.48                |                   | 0.28           | <0.5            | <5              | 2               | 14              | 1120            | 4.93          | 2               | 0.12         | 10             | 52              |
| R3888                    | 2.48                |                   | 0.01           | <0.5            | <5              | <2              | 15              | 26              | 5.17          | <2              | 0.01         | 10             | 59              |
| R3889                    | 2.45                |                   | 0.02           | <0.5            | <5              | <2              | 16              | 593             | 5.25          | <2              | 0.06         | <10            | 61              |
| R3890                    | 2.56                |                   | 0.66           | <0.5            | <5              | 3               | 16              | 2190            | 5.57          | <2              | 0.33         | 10             | 55              |
| R3891                    | 2.63                |                   | 1.11           | 0.6             | 7               | 138             | 25              | 3340            | 6.24          | 7               | 0.49         | 10             | 74              |
| R3892                    | 2.56                |                   | 2.45           | 0.6             | <5              | 166             | 19              | 3590            | 5.86          | 7               | 0.38         | 10             | 66              |
| R3893                    | 2.46                |                   | 4.74           | 1.4             | <5              | 631             | 16              | 6280            | 5.30          | 17              | 0.65         | 10             | 58              |
| R3894                    | 2.64                |                   | 2.86           | 1.4             | <5              | 574             | 16              | 3930            | 5.72          | 19              | 0.39         | 10             | 73              |
| R3895                    | 2.55                |                   | 0.02           | <0.5            | <5              | 4               | 20              | 52              | 6.84          | <2              | 0.01         | 10             | 129             |
| R3896                    | 2.45                |                   | 0.03           | <0.5            | <5              | 4               | 16              | 45              | 5.60          | <2              | 0.01         | 10             | 105             |
| R3897                    | 2.47                |                   | 0.12           | <0.5            | 6               | 5               | 14              | 176             | 4.71          | 3               | 0.02         | 10             | 84              |
| R3898                    | 2.57                |                   | <0.01          | <0.5            | 6               | <2              | 13              | 7               | 4.52          | 5               | 0.01         | 10             | 77              |
| R3899                    | 2.56                |                   | <0.01          | <0.5            | <5              | <2              | 16              | 13              | 5.56          | 2               | 0.01         | 10             | 108             |
| R3900                    | 0.12                |                   | 0.61           | 1.5             | 7               | 4               | 12              | 5190            | 4.68          | 8               | 0.63         | <10            | 57              |
| R3901                    | 2.50                |                   | <0.01          | <0.5            | <5              | <2              | 17              | 12              | 5.79          | <2              | 0.01         | 10             | 117             |
| R3902                    | 2.46                |                   | <0.01          | <0.5            | <5              | <2              | 16              | 35              | 5.34          | 2               | 0.01         | 10             | 104             |
| R3903                    | 2.58                |                   | <0.01          | <0.5            | <5              | <2              | 16              | 6               | 5.33          | <2              | 0.01         | 10             | 93              |
| R3904                    | 2.62                |                   | 0.04           | <0.5            | <5              | <2              | 30              | 19              | 9.63          | <2              | 0.04         | 10             | 188             |
| R3905                    | 2.61                |                   | <0.01          | <0.5            | <5              | <2              | 25              | 47              | 8.37          | <2              | 0.02         | <10            | 166             |
| R3906                    | 2.22                |                   | <0.01          | <0.5            | 5               | <2              | 20              | 4               | 6.57          | <2              | <0.01        | <10            | 136             |